

Type	Photodetector Module	
Model	DX30BF	
Serial Number	U01232	
Dark Current	1	nA
Responsivity @ 850nm MM	0.45	A/W
Optical Return Loss @ 850nm MM	-11	dB
Responsivity @ 1310nm MM	0.75	A/W
Optical Return Loss @ 1310nm MM	-14	dB
FWHM	14.0	ps
3 dB Bandwidth	35.2	GHz
QA		

Additional test data and all other documentation may be found at www.thorlabs.com/manuals (by Model and Serial #)



Caution: This is an ESD Sensitive Component.
 Take all appropriate precautions to discharge personnel and equipment before making any electrical connections to the unit. This especially applies to coaxial connecting cables that can accumulate capacitive charge.