

FINAL INSPECTION REPORT
1x2 75:25 PM Narrowband Coupler

Item #: PN1310R3A1
 SN: T009391

Center Wavelength: 1310 nm
 Coupling Ratio Specification
 Signal Output: 73 % - 77 %
 Tap Output: 23 % - 27 %
 Bandwidth: ±15 nm
 Maximum Optical Power^a
 With Connectors or Bare Fiber: 1 W
 Spliced: 5 W
 Fiber Type: Corning PR PM 13-U25D-H

| Test Data ^b | |
|-----------------------------|---------------------------------------|
| Excess Loss ^c | ≤ 0.5 dB |
| Input-Output Path | White (Input) – White (Signal Output) |
| Coupling Ratio ^d | 74.4 % |
| Insertion Loss ^e | 1.46 dB |
| PER ^f | 27 dB |
| Input-Output Path | White (Input) – Red (Tap Output) |
| Coupling Ratio ^d | 25.6 % |
| Insertion Loss ^e | 6.1 dB |
| PER ^f | 26.5 dB |

- a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.
- b. All values are measured at room temperature without connectors through the white input port.
- c. Ratio of the input optical power to the total optical power from all output ports. It is measured at the center wavelength.
- d. Does not include losses, as this is a measurement of the output power distribution only.
- e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.
- f. Measured with a slow axis launch at room temperature with connectors at the center wavelength through the white input port.