

# LASER OPTICAL DENSITY CERTIFICATION

## M AB8

Supplier: Thorlabs Limited  
Purchase Order Number: EO-396767  
Part Number: F002  
Requirements: EN 12254: 2010(E), Paragraph 5.3 Resistance to Laser Radiation, Table 2. 315-1400 nm Range.

Cert. Number: 59998  
Date: August 29, 2018

### TEST PARAMETERS

Coating Type: N/A  
Test Wavelength: 1064 nm / 532 nm  
Polarization: Random  
Pulsewidth (square): 500 ps / 400 ps  
Spot Diameter (1/e): 0.949 / 0.904 mm  
Test Prep: N<sub>2</sub> blow  
Quantity: 3

Substrate Material: Fabric  
Incidence Angle: 0°  
PRF : 20 Hz  
Transverse Mode: TEM<sub>00</sub>  
Axial Modes: Multiple  
Number of Sites: 1  
Exposure Duration: 50 seconds

### TEST RESULTS:

<u>Sample</u>	<u>Measurement Level</u>
25	Sample maintains AB8 during irradiation.
26	Sample maintains AB8 during irradiation.
27	Sample maintains AB8 during irradiation.

COMMENTS: Laser penetrates samples at AB8.5 levels.

**Spica Technologies certifies that this sample has been exposed to the parameters described above. All test and calibration data are maintained on file. All instrument calibration is traceable to NIST.**

Test conducted by \_\_\_\_\_



**Spica**  
Technologies Inc.

18 Clinton Drive #3  
Hollis, NH 03049  
[www.spicatech.com](http://www.spicatech.com)  
603-882-8233