

LASER OPTICAL DENSITY CERTIFICATION

R AB7

Supplier: Thorlabs Limited
Purchase Order Number: EO-265946
Requirements: EN 12254: 2010(E), Paragraph 5.3 Resistance to Laser Radiation, Table 2. 315-1400 nm Range.

Cert. Number: 51498
Date: September 23, 2015

TEST PARAMETERS

Coating Type: N/A	Substrate Material: Fabric
Test Wavelength: 1064 nm	Incidence Angle: 0°
Polarization: Random	PRF : 20 Hz
Pulsewidth (square): 2 ms	Transverse Mode: TEM ₀₀
Spot Diameter (1/e): 1.008 mm	Axial Modes: Multiple
Test Prep: N ₂ blow	Number of Sites: 1
Quantity: 3	Exposure Duration: 1000 shots/site

TEST RESULTS:

<u>Sample</u>	<u>Measurement Level</u>
8	Sample maintains AB7 during irradiation.
8	Sample maintains AB7 during irradiation.
8	Sample maintains AB7 during irradiation.

COMMENTS: Laser penetrates samples at AB8.

Spica Technologies certifies that this sample has been exposed to the parameters described above. All test and calibration data are maintained on file. All instrument calibration is traceable to NIST.

Test conducted by _____



Spica
Technologies Inc.

18 Clinton Drive #3
Hollis, NH 03049
www.spicatech.com
603-882-8233